

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250941

Luminaire Tested: P3AS02R609030DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609030DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250941

CATALOG NUMBER: P3AS02R609030DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250941

CATALOG NUMBER: P3AS02R609030DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88	86	84	82
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75	72	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	61	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	67	62	58	76	67	61	58	66	61	57		65	61	57		64	60	57	56
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76507
5°	72221
10°	70339
15°	68740
20°	63916
25°	57124
30°	43652
35°	25190
40°	9790
45°	4062
50°	887
55°	153
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4062 cd/sqm

TEST NUMBER: P1250941

CATALOG NUMBER: P3AS02R609030DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	10.6
10°-20°	84.3	28.9
20°-30°	105.6	36.2
30°-40°	59.1	20.2
40°-50°	11.2	3.8
50°-60°	0.6	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.0	75.7
0°-40°	280.0	95.9
0°-60°	291.8	99.9
0°-90°	292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	349	
5°	328	31
15°	303	84
25°	236	106
35°	94	59
45°	13	11
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1250941

CATALOG NUMBER: P3AS02R609030DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	348.9
1°	347.5
2°	342.9
3°	337.6
4°	332.5
5°	328.1
6°	324.8
7°	321.9
8°	319.8
9°	317.7
10°	315.9
11°	314.1
12°	312.1
13°	309.6
14°	306.6
15°	302.8
16°	298.1
17°	292.9
18°	286.9
19°	280.1
20°	273.9
21°	267.2
22°	260.3
23°	253.0
24°	245.0
25°	236.1
26°	225.8
27°	214.2
28°	201.1
29°	187.3
30°	172.4
31°	157.3
32°	141.8
32.5°	133.3
33°	125.7
34°	109.8
35°	94.1
36°	80.0
37°	65.1
37.5°	58.3
38°	51.6
39°	41.6
40°	34.2
42.5°	20.8
45°	13.1

TEST NUMBER: P1250941

CATALOG NUMBER: P3AS02R609030DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.3
50°	2.6
52.5°	0.6
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)