

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252157

Luminaire Tested: P3AS13R659030DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659030DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1159.0 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252157

CATALOG NUMBER: P3AS13R659030DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1252157

CATALOG NUMBER: P3AS13R659030DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	310567
5°	288355
10°	278864
15°	268742
20°	248452
25°	226368
30°	174888
35°	101375
40°	40218
45°	17149
50°	4060
55°	535
60°	439
65°	259
70°	321
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17149 cd/sqm

TEST NUMBER: P1252157

CATALOG NUMBER: P3AS13R659030DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.6	10.7
10°-20°	329.9	28.5
20°-30°	417.5	36.0
30°-40°	237.7	20.5
40°-50°	47.2	4.1
50°-60°	2.5	0.2
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	870.9	75.1
0°-40°	1108.6	95.6
0°-60°	1158.3	99.9
0°-90°	1159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1416	
5°	1310	124
15°	1184	330
25°	936	417
35°	379	238
45°	55	47
55°	1	2
65°	0	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252157

CATALOG NUMBER: P3AS13R659030DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1416.3
1°	1405.8
2°	1382.9
3°	1356.3
4°	1330.0
5°	1310.0
6°	1295.3
7°	1283.4
8°	1272.9
9°	1262.4
10°	1252.4
11°	1241.4
12°	1230.0
13°	1216.2
14°	1201.4
15°	1183.8
16°	1162.8
17°	1140.0
18°	1115.2
19°	1089.0
20°	1064.7
21°	1039.9
22°	1017.5
23°	994.2
24°	967.0
25°	935.6
26°	898.0
27°	852.7
28°	801.7
29°	747.4
30°	690.7
31°	628.3
32°	566.4
32.5°	534.5
33°	503.5
34°	440.7
35°	378.7
36°	321.6
37°	264.9
37.5°	235.8
38°	212.5
39°	172.0
40°	140.5
42.5°	86.7
45°	55.3

TEST NUMBER: P1252157

CATALOG NUMBER: P3AS13R659030DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	32.4
50°	11.9
52.5°	2.4
55°	1.4
57.5°	1.0
60°	1.0
62.5°	1.0
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)