

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252161

Luminaire Tested: P3AS13R659030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 478.0 lumens
Efficiency: N/A
Efficacy: 32.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252161
CATALOG NUMBER: P3AS13R659030DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1252161
 CATALOG NUMBER: P3AS13R659030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112732
5°	111380
10°	107146
15°	100364
20°	90285
25°	76650
30°	59959
35°	42724
40°	27967
45°	17273
50°	8767
55°	3097
60°	2719
65°	2698
70°	2436
75°	2457
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17273 cd/sqm



TEST NUMBER: P1252161
 CATALOG NUMBER: P3AS13R659030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.5	9.9
10°-20°	123.1	25.7
20°-30°	143.8	30.1
30°-40°	100.5	21.0
40°-50°	44.2	9.3
50°-60°	9.8	2.1
60°-70°	5.0	1.0
70°-80°	3.0	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.4	65.8
0°-40°	414.9	86.8
0°-60°	468.9	98.1
0°-90°	478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	514	
5°	506	48
15°	442	123
25°	317	144
35°	160	100
45°	56	44
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1252161
CATALOG NUMBER: P3AS13R659030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	514.1
2.5°	512.2
5°	506.0
7.5°	495.5
10°	481.2
12.5°	463.6
15°	442.1
17.5°	415.9
20°	386.9
22.5°	354.0
25°	316.8
27.5°	277.8
30°	236.8
32.5°	197.2
35°	159.6
37.5°	126.7
40°	97.7
42.5°	73.8
45°	55.7
47.5°	41.0
50°	25.7
52.5°	13.3
55°	8.1
57.5°	7.1
60°	6.2
62.5°	5.7
65°	5.2
67.5°	4.3
70°	3.8
72.5°	3.3
75°	2.9
77.5°	2.4
80°	1.9
82.5°	1.4
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)