

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251033

Luminaire Tested: P3AS05R109030DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109030DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 447.0 lumens
Efficiency: N/A
Efficacy: 56.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251033

CATALOG NUMBER: P3AS05R109030DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251033

CATALOG NUMBER: P3AS05R109030DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	381855
5°	338960
10°	235400
15°	139206
20°	79294
25°	45317
30°	25067
35°	13385
40°	7385
45°	4000
50°	2490
55°	1988
60°	1710
65°	1557
70°	1410
75°	1440
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4000 cd/sqm

TEST NUMBER: P1251033

CATALOG NUMBER: P3AS05R109030DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.9	29.3
10°-20°	172.8	38.7
20°-30°	89.0	19.9
30°-40°	33.4	7.5
40°-50°	10.9	2.4
50°-60°	4.7	1.1
60°-70°	3.0	0.7
70°-80°	1.8	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	392.7	87.9
0°-40°	426.1	95.3
0°-60°	441.8	98.8
0°-90°	447.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	447.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1741	
5°	1540	131
15°	613	173
25°	187	89
35°	50	33
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1251033

CATALOG NUMBER: P3AS05R109030DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1741.4
1°	1738.0
2°	1715.1
3°	1671.6
4°	1614.4
5°	1539.9
6°	1455.5
7°	1362.9
8°	1260.0
9°	1158.3
10°	1057.2
12.5°	813.4
15°	613.2
17.5°	459.0
20°	339.8
22.5°	253.6
25°	187.3
27.5°	136.5
30°	99.0
32.5°	70.2
35°	50.0
37.5°	35.7
40°	25.8
42.5°	18.5
45°	12.9
47.5°	9.5
50°	7.3
52.5°	6.0
55°	5.2
57.5°	4.3
60°	3.9
62.5°	3.4
65°	3.0
67.5°	2.6
70°	2.2
72.5°	2.2
75°	1.7
77.5°	1.3
80°	0.9
82.5°	0.9
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)