

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252182

Luminaire Tested: P3AS13R709030DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252182
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709030DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1215.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252182
CATALOG NUMBER: P3AS13R709030DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1252182
 CATALOG NUMBER: P3AS13R709030DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241275
5°	230222
10°	219034
15°	213191
20°	205305
25°	194310
30°	180737
35°	151808
40°	97840
45°	45462
50°	11940
55°	2982
60°	2982
65°	2542
70°	2500
75°	2457
80°	2399
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 45462 cd/sqm



TEST NUMBER: P1252182
 CATALOG NUMBER: P3AS13R709030DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.9	8.1
10°-20°	263.9	21.7
20°-30°	368.7	30.3
30°-40°	341.8	28.1
40°-50°	122.6	10.1
50°-60°	10.4	0.9
60°-70°	5.2	0.4
70°-80°	3.3	0.3
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.4	60.1
0°-40°	1072.2	88.2
0°-60°	1205.2	99.2
0°-90°	1215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1100	
5°	1046	98
15°	939	264
25°	803	369
35°	567	342
45°	147	123
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1252182
CATALOG NUMBER: P3AS13R709030DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1100.3
2.5°	1083.8
5°	1045.9
7.5°	1010.9
10°	983.7
12.5°	961.4
15°	939.1
17.5°	911.9
20°	879.8
22.5°	842.9
25°	803.1
27.5°	762.3
30°	713.8
32.5°	651.6
35°	567.1
37.5°	459.3
40°	341.8
42.5°	233.1
45°	146.6
47.5°	81.6
50°	35.0
52.5°	11.7
55°	7.8
57.5°	6.8
60°	6.8
62.5°	5.8
65°	4.9
67.5°	4.9
70°	3.9
72.5°	3.9
75°	2.9
77.5°	2.9
80°	1.9
82.5°	1.9
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)