

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251038

Luminaire Tested: P3AS05R109030DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109030DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 265.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251038
CATALOG NUMBER: P3AS05R109030DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1251038
 CATALOG NUMBER: P3AS05R109030DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114267
5°	105613
10°	84323
15°	63701
20°	48491
25°	36970
30°	26485
35°	17266
40°	10591
45°	6419
50°	4264
55°	3288
60°	2851
65°	2439
70°	2180
75°	2203
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6419 cd/sqm



TEST NUMBER: P1251038
 CATALOG NUMBER: P3AS05R109030DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.5	16.0
10°-20°	78.4	29.6
20°-30°	69.8	26.4
30°-40°	41.3	15.6
40°-50°	16.9	6.4
50°-60°	8.0	3.0
60°-70°	4.8	1.8
70°-80°	2.5	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.7	72.0
0°-40°	232.1	87.6
0°-60°	257.0	97.0
0°-90°	265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	265.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	521	
5°	480	43
15°	281	78
25°	153	70
35°	64	41
45°	21	17
55°	9	8
65°	5	5
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1251038
CATALOG NUMBER: P3AS05R109030DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	521.1
1°	519.8
2°	516.0
3°	508.2
4°	495.3
5°	479.8
6°	463.0
7°	443.2
8°	422.6
9°	401.5
10°	378.7
12.5°	326.6
15°	280.6
17.5°	241.0
20°	207.8
22.5°	178.6
25°	152.8
27.5°	127.8
30°	104.6
32.5°	83.5
35°	64.5
37.5°	49.5
40°	37.0
42.5°	27.5
45°	20.7
47.5°	15.9
50°	12.5
52.5°	10.3
55°	8.6
57.5°	7.3
60°	6.5
62.5°	5.6
65°	4.7
67.5°	4.3
70°	3.4
72.5°	3.0
75°	2.6
77.5°	1.7
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)