

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252190

Luminaire Tested: P3AS13R709030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252190
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 480.1 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252190

CATALOG NUMBER: P3AS13R709030DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1252190

CATALOG NUMBER: P3AS13R709030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92931
5°	91811
10°	89154
15°	85381
20°	79970
25°	72657
30°	62769
35°	50032
40°	36440
45°	23940
50°	11224
55°	3479
60°	3333
65°	3217
70°	3077
75°	3219
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23940 cd/sqm

TEST NUMBER: P1252190

CATALOG NUMBER: P3AS13R709030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	8.2
10°-20°	105.3	21.9
20°-30°	136.8	28.5
30°-40°	116.1	24.2
40°-50°	59.8	12.5
50°-60°	11.5	2.4
60°-70°	6.3	1.3
70°-80°	3.9	0.8
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.3	58.6
0°-40°	397.4	82.8
0°-60°	468.8	97.7
0°-90°	480.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	480.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	424	
5°	417	39
15°	376	105
25°	300	137
35°	187	116
45°	77	60
55°	9	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252190

CATALOG NUMBER: P3AS13R709030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	423.8
2.5°	422.3
5°	417.1
7.5°	409.5
10°	400.4
12.5°	389.0
15°	376.1
17.5°	360.4
20°	342.7
22.5°	322.7
25°	300.3
27.5°	275.0
30°	247.9
32.5°	217.8
35°	186.9
37.5°	156.4
40°	127.3
42.5°	100.1
45°	77.2
47.5°	56.7
50°	32.9
52.5°	14.3
55°	9.1
57.5°	8.6
60°	7.6
62.5°	7.2
65°	6.2
67.5°	5.7
70°	4.8
72.5°	4.3
75°	3.8
77.5°	2.9
80°	2.4
82.5°	1.4
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)