

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252221

Luminaire Tested: P3AS17R129030DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252221  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R129030DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1112.0 lumens  
Efficiency: N/A  
Efficacy: 48.6 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 22.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252221  
CATALOG NUMBER: P3AS17R129030DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1252221  
 CATALOG NUMBER: P3AS17R129030DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	949946
5°	843207
10°	585583
15°	346290
20°	197230
25°	112748
30°	62389
35°	33274
40°	18406
45°	9955
50°	6209
55°	4932
60°	4210
65°	3891
70°	3462
75°	3643
80°	2652
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9955 cd/sqm



TEST NUMBER: P1252221  
 CATALOG NUMBER: P3AS17R129030DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	325.8	29.3
10°-20°	429.9	38.7
20°-30°	221.4	19.9
30°-40°	83.1	7.5
40°-50°	27.2	2.4
50°-60°	11.7	1.1
60°-70°	7.4	0.7
70°-80°	4.4	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.0	87.9
0°-40°	1060.1	95.3
0°-60°	1099.1	98.8
0°-90°	1112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1112.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4332	
5°	3831	326
15°	1525	430
25°	466	221
35°	124	83
45°	32	27
55°	13	12
65°	8	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1252221  
CATALOG NUMBER: P3AS17R129030DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4332.1
1°	4323.5
2°	4266.7
3°	4158.5
4°	4016.1
5°	3830.7
6°	3620.8
7°	3390.5
8°	3134.4
9°	2881.6
10°	2629.9
12.5°	2023.6
15°	1525.4
17.5°	1141.9
20°	845.2
22.5°	631.0
25°	466.0
27.5°	339.6
30°	246.4
32.5°	174.6
35°	124.3
37.5°	88.9
40°	64.3
42.5°	46.1
45°	32.1
47.5°	23.6
50°	18.2
52.5°	15.0
55°	12.9
57.5°	10.7
60°	9.6
62.5°	8.6
65°	7.5
67.5°	6.4
70°	5.4
72.5°	5.4
75°	4.3
77.5°	3.2
80°	2.1
82.5°	2.1
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)