

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252226

Luminaire Tested: P3AS17R129030DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129030DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 846.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252226
CATALOG NUMBER: P3AS17R129030DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1252226
 CATALOG NUMBER: P3AS17R129030DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213382
5°	207594
10°	189709
15°	166176
20°	142556
25°	119015
30°	95255
35°	71447
40°	51840
45°	33895
50°	21219
55°	14336
60°	12674
65°	11674
70°	10963
75°	9997
80°	9471
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33895 cd/sqm



TEST NUMBER: P1252226
 CATALOG NUMBER: P3AS17R129030DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	10.3
10°-20°	204.0	24.1
20°-30°	224.7	26.6
30°-40°	168.3	19.9
40°-50°	87.2	10.3
50°-60°	36.2	4.3
60°-70°	22.4	2.6
70°-80°	12.6	1.5
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.7	61.0
0°-40°	684.0	80.9
0°-60°	807.4	95.4
0°-90°	846.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	846.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	973	
5°	943	87
15°	732	204
25°	492	225
35°	267	168
45°	109	87
55°	38	36
65°	22	22
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1252226
CATALOG NUMBER: P3AS17R129030DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	973.1
1°	974.2
2°	971.0
3°	964.6
4°	954.9
5°	943.1
6°	928.1
7°	912.1
8°	892.8
9°	872.4
10°	852.0
12.5°	793.1
15°	732.0
17.5°	670.9
20°	610.9
22.5°	549.8
25°	491.9
27.5°	434.1
30°	376.2
32.5°	319.4
35°	266.9
37.5°	221.9
40°	181.1
42.5°	143.6
45°	109.3
47.5°	82.5
50°	62.2
52.5°	46.1
55°	37.5
57.5°	33.2
60°	28.9
62.5°	25.7
65°	22.5
67.5°	19.3
70°	17.1
72.5°	13.9
75°	11.8
77.5°	9.6
80°	7.5
82.5°	5.4
85°	3.2
87.5°	1.1
90°	0.0

(END OF REPORT)