

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252233

Luminaire Tested: P3AS17R129030DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129030DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 827.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252233

CATALOG NUMBER: P3AS17R129030DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1252233

CATALOG NUMBER: P3AS17R129030DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240661
5°	225599
10°	184989
15°	143724
20°	113457
25°	90417
30°	72568
35°	59240
40°	48806
45°	41059
50°	35274
55°	30508
60°	27059
65°	23556
70°	20965
75°	16945
80°	13764
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41059 cd/sqm

TEST NUMBER: P1252233

CATALOG NUMBER: P3AS17R129030DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	11.1
10°-20°	177.3	21.4
20°-30°	172.4	20.8
30°-40°	139.3	16.8
40°-50°	103.4	12.5
50°-60°	72.3	8.7
60°-70°	45.3	5.5
70°-80°	21.5	2.6
80°-90°	3.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.2	53.4
0°-40°	580.6	70.2
0°-60°	756.3	91.4
0°-90°	827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	827.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1098	
5°	1025	92
15°	633	177
25°	374	172
35°	221	139
45°	132	103
55°	80	72
65°	45	45
75°	20	22
85°	4	4
90°	0	

TEST NUMBER: P1252233

CATALOG NUMBER: P3AS17R129030DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1097.5
2.5°	1079.4
5°	1024.9
7.5°	937.9
10°	830.8
12.5°	725.6
15°	633.1
17.5°	555.1
20°	486.2
22.5°	426.3
25°	373.7
27.5°	326.5
30°	286.6
32.5°	252.2
35°	221.3
37.5°	194.1
40°	170.5
42.5°	150.6
45°	132.4
47.5°	117.9
50°	103.4
52.5°	90.7
55°	79.8
57.5°	70.7
60°	61.7
62.5°	52.6
65°	45.4
67.5°	38.1
70°	32.7
72.5°	25.4
75°	20.0
77.5°	14.5
80°	10.9
82.5°	5.4
85°	3.6
87.5°	0.0
90°	0.0

(END OF REPORT)