

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252234

Luminaire Tested: P3AS17R129030DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129030DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 584.9 lumens
Efficiency: N/A
Efficacy: 25.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252234

CATALOG NUMBER: P3AS17R129030DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1252234

CATALOG NUMBER: P3AS17R129030DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218952
5°	201034
10°	160184
15°	119706
20°	90915
25°	68835
30°	50945
35°	36379
40°	24904
45°	17428
50°	14840
55°	14566
60°	15087
65°	15981
70°	16285
75°	16860
80°	18310
85°	18115

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 21336 cd/sqm

TEST NUMBER: P1252234

CATALOG NUMBER: P3AS17R129030DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	13.8
10°-20°	147.9	25.3
20°-30°	131.0	22.4
30°-40°	85.8	14.7
40°-50°	45.9	7.8
50°-60°	34.7	5.9
60°-70°	29.8	5.1
70°-80°	20.5	3.5
80°-90°	8.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.8	61.5
0°-40°	445.6	76.2
0°-60°	526.2	90.0
0°-90°	584.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	584.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	998	
5°	913	81
15°	527	148
25°	284	131
35°	136	86
45°	56	46
55°	38	35
65°	31	30
75°	20	21
85°	7	8
90°	0	

TEST NUMBER: P1252234

CATALOG NUMBER: P3AS17R129030DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	998.5
2.5°	975.0
5°	913.3
7.5°	822.7
10°	719.4
12.5°	619.8
15°	527.3
17.5°	453.0
20°	389.6
22.5°	333.4
25°	284.5
27.5°	241.0
30°	201.2
32.5°	166.7
35°	135.9
37.5°	108.7
40°	87.0
42.5°	68.9
45°	56.2
47.5°	48.9
50°	43.5
52.5°	41.7
55°	38.1
57.5°	36.2
60°	34.4
62.5°	32.6
65°	30.8
67.5°	27.2
70°	25.4
72.5°	21.7
75°	19.9
77.5°	16.3
80°	14.5
82.5°	12.7
85°	7.2
87.5°	3.6
90°	0.0

(END OF REPORT)