

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252252

Luminaire Tested: P3AS17R159030DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159030DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 498.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252252
CATALOG NUMBER: P3AS17R159030DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1252252
 CATALOG NUMBER: P3AS17R159030DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65				65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60				60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56				56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52				52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49				49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125604
5°	122210
10°	111688
15°	97821
20°	83914
25°	70069
30°	56059
35°	42054
40°	30514
45°	19971
50°	12486
55°	8449
60°	7456
65°	6849
70°	6475
75°	5846
80°	5556
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19971 cd/sqm



TEST NUMBER: P1252252
 CATALOG NUMBER: P3AS17R159030DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.2	10.3
10°-20°	120.1	24.1
20°-30°	132.3	26.6
30°-40°	99.1	19.9
40°-50°	51.4	10.3
50°-60°	21.3	4.3
60°-70°	13.2	2.6
70°-80°	7.4	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	303.6	61.0
0°-40°	402.6	80.9
0°-60°	475.3	95.4
0°-90°	498.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	498.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	573	
5°	555	51
15°	431	120
25°	290	132
35°	157	99
45°	64	51
55°	22	21
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1252252
CATALOG NUMBER: P3AS17R159030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	572.8
1°	573.5
2°	571.6
3°	567.8
4°	562.1
5°	555.2
6°	546.3
7°	536.9
8°	525.5
9°	513.5
10°	501.6
12.5°	466.9
15°	430.9
17.5°	394.9
20°	359.6
22.5°	323.6
25°	289.6
27.5°	255.5
30°	221.4
32.5°	188.0
35°	157.1
37.5°	130.6
40°	106.6
42.5°	84.5
45°	64.4
47.5°	48.6
50°	36.6
52.5°	27.1
55°	22.1
57.5°	19.6
60°	17.0
62.5°	15.1
65°	13.2
67.5°	11.4
70°	10.1
72.5°	8.2
75°	6.9
77.5°	5.7
80°	4.4
82.5°	3.2
85°	1.9
87.5°	0.6
90°	0.0

(END OF REPORT)