

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251191

Luminaire Tested: P3AS05R309030DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309030DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 323.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251191

CATALOG NUMBER: P3AS05R309030DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1251191

CATALOG NUMBER: P3AS05R309030DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		68	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110386
5°	106933
10°	96346
15°	79705
20°	61699
25°	46285
30°	33600
35°	22379
40°	13769
45°	8063
50°	4947
55°	4014
60°	3508
65°	2854
70°	2565
75°	2542
80°	1894
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8063 cd/sqm

TEST NUMBER: P1251191

CATALOG NUMBER: P3AS05R309030DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	13.8
10°-20°	96.7	29.9
20°-30°	88.0	27.2
30°-40°	53.2	16.5
40°-50°	21.3	6.6
50°-60°	9.4	2.9
60°-70°	5.7	1.8
70°-80°	3.1	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	229.4	71.0
0°-40°	282.5	87.5
0°-60°	313.3	97.0
0°-90°	323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	503	
5°	486	45
15°	351	97
25°	191	88
35°	84	53
45°	26	21
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1251191

CATALOG NUMBER: P3AS05R309030DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	503.4
1°	502.9
2°	500.8
3°	497.3
4°	492.3
5°	485.8
6°	477.8
7°	469.3
8°	458.3
9°	445.8
10°	432.7
11°	417.7
12°	401.7
13°	385.7
14°	368.1
15°	351.1
17.5°	306.5
20°	264.4
22.5°	225.4
25°	191.3
27.5°	160.3
30°	132.7
32.5°	107.2
35°	83.6
37.5°	64.1
40°	48.1
42.5°	35.1
45°	26.0
47.5°	19.5
50°	14.5
52.5°	11.5
55°	10.5
57.5°	9.0
60°	8.0
62.5°	6.5
65°	5.5
67.5°	5.0
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.5
80°	1.5
82.5°	1.0
85°	1.0
87.5°	0.5



TEST NUMBER: P1251191

CATALOG NUMBER: P3AS05R309030DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)