

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251216

Luminaire Tested: P3AS05R359030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 405.0 lumens
Efficiency: N/A
Efficacy: 56.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251216

CATALOG NUMBER: P3AS05R359030DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251216

CATALOG NUMBER: P3AS05R359030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92515
5°	90557
10°	84813
15°	76118
20°	66226
25°	56423
30°	47273
35°	37638
40°	27222
45°	17242
50°	9381
55°	6499
60°	6140
65°	5707
70°	5450
75°	4660
80°	4420
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 17242 cd/sqm

TEST NUMBER: P1251216

CATALOG NUMBER: P3AS05R359030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	9.5
10°-20°	93.3	23.0
20°-30°	106.9	26.4
30°-40°	87.3	21.5
40°-50°	44.0	10.9
50°-60°	16.3	4.0
60°-70°	10.9	2.7
70°-80°	6.1	1.5
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	238.5	58.9
0°-40°	325.8	80.4
0°-60°	386.1	95.3
0°-90°	405.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	405.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	422	
5°	411	38
15°	335	93
25°	233	107
35°	141	87
45°	56	44
55°	17	16
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1251216

CATALOG NUMBER: P3AS05R359030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	421.9
1°	421.4
2°	420.4
3°	418.4
4°	415.4
5°	411.4
6°	406.4
7°	401.4
8°	394.9
9°	388.4
10°	380.9
11°	372.9
12°	364.3
13°	354.8
14°	344.8
15°	335.3
17.5°	309.8
20°	283.8
22.5°	257.2
25°	233.2
27.5°	209.7
30°	186.7
32.5°	163.7
35°	140.6
37.5°	117.6
40°	95.1
42.5°	74.1
45°	55.6
47.5°	40.0
50°	27.5
52.5°	20.0
55°	17.0
57.5°	15.5
60°	14.0
62.5°	12.5
65°	11.0
67.5°	9.5
70°	8.5
72.5°	7.0
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	1.0



TEST NUMBER: P1251216

CATALOG NUMBER: P3AS05R359030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)