

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251221

Luminaire Tested: P3AS05R359030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 526.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251221

CATALOG NUMBER: P3AS05R359030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1251221

CATALOG NUMBER: P3AS05R359030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	69	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265286
5°	254963
10°	222151
15°	170149
20°	113830
25°	68883
30°	39525
35°	22111
40°	11736
45°	6047
50°	2900
55°	2294
60°	2193
65°	1816
70°	1923
75°	1694
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6047 cd/sqm

TEST NUMBER: P1251221

CATALOG NUMBER: P3AS05R359030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	20.0
10°-20°	204.2	38.8
20°-30°	133.7	25.4
30°-40°	54.2	10.3
40°-50°	16.3	3.1
50°-60°	5.5	1.1
60°-70°	3.7	0.7
70°-80°	2.2	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	443.3	84.3
0°-40°	497.6	94.6
0°-60°	519.3	98.7
0°-90°	526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1210	
5°	1158	105
15°	750	204
25°	285	134
35°	83	54
45°	20	16
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1251221

CATALOG NUMBER: P3AS05R359030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1209.8
1°	1207.8
2°	1202.3
3°	1191.3
4°	1178.3
5°	1158.3
6°	1133.3
7°	1105.3
8°	1073.7
9°	1037.7
10°	997.7
11°	953.2
12°	906.6
13°	854.6
14°	805.0
15°	749.5
17.5°	614.9
20°	487.8
22.5°	375.3
25°	284.7
27.5°	212.1
30°	156.1
32.5°	114.6
35°	82.6
37.5°	58.5
40°	41.0
42.5°	28.5
45°	19.5
47.5°	13.0
50°	8.5
52.5°	6.5
55°	6.0
57.5°	5.5
60°	5.0
62.5°	4.5
65°	3.5
67.5°	3.0
70°	3.0
72.5°	2.5
75°	2.0
77.5°	1.5
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5



TEST NUMBER: P1251221

CATALOG NUMBER: P3AS05R359030DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)