

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252304

Luminaire Tested: P3AS17R259030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 661.0 lumens
Efficiency: N/A
Efficacy: 31.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252304
CATALOG NUMBER: P3AS17R259030DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1252304

CATALOG NUMBER: P3AS17R259030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	424001
5°	395597
10°	316895
15°	215098
20°	130165
25°	76117
30°	43348
35°	23851
40°	12652
45°	6667
50°	3889
55°	2906
60°	2500
65°	2646
70°	2436
75°	2118
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6667 cd/sqm



TEST NUMBER: P1252304
 CATALOG NUMBER: P3AS17R259030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.5	24.1
10°-20°	260.5	39.4
20°-30°	148.9	22.5
30°-40°	58.7	8.9
40°-50°	18.0	2.7
50°-60°	7.1	1.1
60°-70°	4.8	0.7
70°-80°	2.7	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	568.8	86.1
0°-40°	627.6	94.9
0°-60°	652.7	98.7
0°-90°	661.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1934	
5°	1797	159
15°	948	261
25°	315	149
35°	89	59
45°	22	18
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1252304
CATALOG NUMBER: P3AS17R259030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1933.6
1°	1929.8
2°	1914.0
3°	1886.2
4°	1847.7
5°	1797.2
6°	1737.8
7°	1670.8
8°	1593.1
9°	1513.5
10°	1423.2
11°	1334.1
12°	1236.2
13°	1139.6
14°	1040.4
15°	947.5
17.5°	734.7
20°	557.8
22.5°	418.8
25°	314.6
27.5°	233.1
30°	171.2
32.5°	123.8
35°	89.1
37.5°	63.2
40°	44.2
42.5°	30.3
45°	21.5
47.5°	15.2
50°	11.4
52.5°	8.8
55°	7.6
57.5°	6.9
60°	5.7
62.5°	5.1
65°	5.1
67.5°	4.4
70°	3.8
72.5°	3.2
75°	2.5
77.5°	1.9
80°	1.3
82.5°	1.3
85°	0.6
87.5°	0.6



TEST NUMBER: P1252304
CATALOG NUMBER: P3AS17R259030DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)