

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251261

Luminaire Tested: P3AS05R459030DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459030DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 671.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251261
CATALOG NUMBER: P3AS05R459030DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1251261
 CATALOG NUMBER: P3AS05R459030DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75		
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290920
5°	292471
10°	283473
15°	237550
20°	181596
25°	110547
30°	46007
35°	14723
40°	4580
45°	930
50°	682
55°	765
60°	658
65°	778
70°	641
75°	847
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 930 cd/sqm



TEST NUMBER: P1251261
 CATALOG NUMBER: P3AS05R459030DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.3	18.7
10°-20°	287.6	42.9
20°-30°	207.1	30.9
30°-40°	43.1	6.4
40°-50°	3.9	0.6
50°-60°	1.6	0.2
60°-70°	1.3	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	620.0	92.4
0°-40°	663.1	98.8
0°-60°	668.6	99.6
0°-90°	671.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	671.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1327	
5°	1329	125
15°	1046	288
25°	457	207
35°	55	43
45°	3	4
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1251261
CATALOG NUMBER: P3AS05R459030DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1326.7
2.5°	1327.2
5°	1328.7
7.5°	1319.2
10°	1273.1
12.5°	1177.0
15°	1046.4
17.5°	912.8
20°	778.2
22.5°	623.6
25°	456.9
27.5°	301.3
30°	181.7
32.5°	101.6
35°	55.0
37.5°	31.0
40°	16.0
42.5°	7.0
45°	3.0
47.5°	2.0
50°	2.0
52.5°	2.0
55°	2.0
57.5°	1.5
60°	1.5
62.5°	1.5
65°	1.5
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)