

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252347

Luminaire Tested: P3AS17R309030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1049.0 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252347

CATALOG NUMBER: P3AS17R309030DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252347

CATALOG NUMBER: P3AS17R309030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	247831
5°	242262
10°	225291
15°	200455
20°	172425
25°	146065
30°	121234
35°	95111
40°	68156
45°	44718
50°	25483
55°	16745
60°	15788
65°	14684
70°	13207
75°	12031
80°	11365
85°	9812

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 44718 cd/sqm

TEST NUMBER: P1252347

CATALOG NUMBER: P3AS17R309030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.2	9.7
10°-20°	245.5	23.4
20°-30°	276.7	26.4
30°-40°	220.9	21.1
40°-50°	113.5	10.8
50°-60°	42.7	4.1
60°-70°	28.0	2.7
70°-80°	15.1	1.4
80°-90°	4.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.3	59.5
0°-40°	845.2	80.6
0°-60°	1001.5	95.5
0°-90°	1049.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1049.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1130	
5°	1101	102
15°	883	245
25°	604	277
35°	355	221
45°	144	114
55°	44	43
65°	28	28
75°	14	15
85°	4	4
90°	0	

TEST NUMBER: P1252347

CATALOG NUMBER: P3AS17R309030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1130.2
1°	1130.2
2°	1126.3
3°	1119.9
4°	1110.9
5°	1100.6
6°	1087.7
7°	1071.0
8°	1053.0
9°	1032.4
10°	1011.8
11°	988.6
12°	964.1
13°	938.4
14°	911.4
15°	883.0
17.5°	811.0
20°	738.9
22.5°	669.4
25°	603.7
27.5°	539.3
30°	478.8
32.5°	417.1
35°	355.3
37.5°	294.8
40°	238.1
42.5°	187.9
45°	144.2
47.5°	106.8
50°	74.7
52.5°	52.8
55°	43.8
57.5°	39.9
60°	36.0
62.5°	32.2
65°	28.3
67.5°	24.5
70°	20.6
72.5°	16.7
75°	14.2
77.5°	11.6
80°	9.0
82.5°	6.4
85°	3.9
87.5°	1.3



TEST NUMBER: P1252347

CATALOG NUMBER: P3AS17R309030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)