

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252357

Luminaire Tested: P3AS17R359030DE010 E3CB1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252357  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R359030DE010 E3CB1MB  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1635.1 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252357  
CATALOG NUMBER: P3AS17R359030DE010 E3CB1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1252357  
 CATALOG NUMBER: P3AS17R359030DE010 E3CB1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1066121
5°	1044417
10°	971614
15°	712354
20°	364755
25°	131475
30°	51198
35°	17935
40°	7385
45°	1985
50°	1774
55°	1988
60°	1710
65°	1349
70°	1667
75°	2203
80°	1642
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 2203 cd/sqm



TEST NUMBER: P1252357  
 CATALOG NUMBER: P3AS17R359030DE010 E3CB1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	442.3	27.1
10°-20°	829.9	50.8
20°-30°	293.8	18.0
30°-40°	51.5	3.1
40°-50°	7.5	0.5
50°-60°	4.2	0.3
60°-70°	3.1	0.2
70°-80°	2.2	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1566.1	95.8
0°-40°	1617.6	98.9
0°-60°	1629.3	99.6
0°-90°	1635.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1635.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4862	
5°	4745	442
15°	3138	830
25°	543	294
35°	67	51
45°	6	8
55°	5	4
65°	3	3
75°	3	2
85°	0	1
90°	0	



TEST NUMBER: P1252357  
CATALOG NUMBER: P3AS17R359030DE010 E3CB1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4861.9
1°	4860.6
2°	4845.2
3°	4815.6
4°	4788.5
5°	4744.8
6°	4699.7
7°	4649.5
8°	4587.7
9°	4491.1
10°	4363.6
11°	4187.2
12°	3974.8
13°	3722.4
14°	3444.3
15°	3137.9
17.5°	2337.0
20°	1563.1
22.5°	942.5
25°	543.4
27.5°	324.5
30°	202.2
32.5°	117.2
35°	67.0
37.5°	42.5
40°	25.8
42.5°	12.9
45°	6.4
47.5°	5.2
50°	5.2
52.5°	5.2
55°	5.2
57.5°	3.9
60°	3.9
62.5°	3.9
65°	2.6
67.5°	2.6
70°	2.6
72.5°	2.6
75°	2.6
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0



TEST NUMBER: P1252357  
CATALOG NUMBER: P3AS17R359030DE010 E3CB1MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)