

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251349

Luminaire Tested: P3AS05R609030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251349
CATALOG NUMBER: P3AS05R609030DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1251349
 CATALOG NUMBER: P3AS05R609030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73				73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60916
5°	60334
10°	58583
15°	54892
20°	48584
25°	40648
30°	31853
35°	23102
40°	15372
45°	9582
50°	5185
55°	1491
60°	1403
65°	1297
70°	1282
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9582 cd/sqm



TEST NUMBER: P1251349
 CATALOG NUMBER: P3AS05R609030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.8	10.0
10°-20°	67.1	26.0
20°-30°	76.5	29.6
30°-40°	54.2	21.0
40°-50°	24.6	9.5
50°-60°	5.2	2.0
60°-70°	2.5	1.0
70°-80°	1.6	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	169.4	65.6
0°-40°	223.6	86.7
0°-60°	253.4	98.2
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	278	
5°	274	26
15°	242	67
25°	168	76
35°	86	54
45°	31	25
55°	4	5
65°	2	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1251349
CATALOG NUMBER: P3AS05R609030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	277.8
2.5°	276.8
5°	274.1
7.5°	269.5
10°	263.1
12.5°	254.0
15°	241.8
17.5°	226.3
20°	208.2
22.5°	188.6
25°	168.0
27.5°	146.9
30°	125.8
32.5°	105.7
35°	86.3
37.5°	69.2
40°	53.7
42.5°	40.7
45°	30.9
47.5°	23.1
50°	15.2
52.5°	7.1
55°	3.9
57.5°	3.4
60°	3.2
62.5°	2.9
65°	2.5
67.5°	2.2
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)