

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251352

Luminaire Tested: P3AS05R609030DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609030DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 527.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251352
CATALOG NUMBER: P3AS05R609030DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1251352

CATALOG NUMBER: P3AS05R609030DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73			73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124442
5°	123266
10°	119659
15°	112123
20°	99222
25°	83013
30°	65073
35°	47194
40°	31402
45°	19568
50°	10609
55°	3058
60°	2851
65°	2594
70°	2565
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19568 cd/sqm



TEST NUMBER: P1251352
 CATALOG NUMBER: P3AS05R609030DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	10.0
10°-20°	137.0	26.0
20°-30°	156.2	29.6
30°-40°	110.8	21.0
40°-50°	50.3	9.5
50°-60°	10.7	2.0
60°-70°	5.1	1.0
70°-80°	3.2	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	345.9	65.6
0°-40°	456.7	86.7
0°-60°	517.6	98.2
0°-90°	527.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	527.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	568	
5°	560	53
15°	494	137
25°	343	156
35°	176	111
45°	63	50
55°	8	11
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1251352
CATALOG NUMBER: P3AS05R609030DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	567.5
2.5°	565.5
5°	560.0
7.5°	550.5
10°	537.4
12.5°	518.9
15°	493.9
17.5°	462.3
20°	425.2
22.5°	385.2
25°	343.1
27.5°	300.0
30°	257.0
32.5°	215.9
35°	176.3
37.5°	141.2
40°	109.7
42.5°	83.1
45°	63.1
47.5°	47.1
50°	31.1
52.5°	14.5
55°	8.0
57.5°	7.0
60°	6.5
62.5°	6.0
65°	5.0
67.5°	4.5
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)