

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251395

Luminaire Tested: P3AS05R659030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 347.0 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251395
CATALOG NUMBER: P3AS05R659030DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1251395
 CATALOG NUMBER: P3AS05R659030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | | | |
| 2 | 107 | 101 | 97 | 93 | 104 | 100 | 96 | 92 | 96 | 93 | 90 | 93 | 91 | 88 | 90 | 88 | 86 | 85 | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 85 | 82 | 87 | 84 | 81 | 85 | 82 | 79 | 78 | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 78 | 74 | 80 | 76 | 73 | 72 | | | |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 77 | 72 | 69 | 75 | 71 | 68 | 66 | | | |
| 6 | 85 | 76 | 69 | 65 | 84 | 75 | 69 | 65 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 66 | 63 | 62 | | | |
| 7 | 81 | 71 | 65 | 60 | 79 | 70 | 64 | 60 | 69 | 64 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 57 | | | |
| 8 | 77 | 67 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 55 | 63 | 58 | 55 | 54 | | | |
| 9 | 73 | 63 | 57 | 52 | 72 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 59 | 55 | 52 | 50 | | | |
| 10 | 69 | 59 | 53 | 49 | 68 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 56 | 52 | 49 | 47 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 88195 |
| 5° | 86000 |
| 10° | 80092 |
| 15° | 71782 |
| 20° | 62002 |
| 25° | 51559 |
| 30° | 40664 |
| 35° | 30142 |
| 40° | 20753 |
| 45° | 12870 |
| 50° | 6993 |
| 55° | 4396 |
| 60° | 3728 |
| 65° | 3373 |
| 70° | 2885 |
| 75° | 2542 |
| 80° | 2526 |
| 85° | 2516 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12870 cd/sqm



TEST NUMBER: P1251395
 CATALOG NUMBER: P3AS05R659030DE010 E3DLP1WMH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 36.3 | 10.5 |
| 10°-20° | 87.9 | 25.3 |
| 20°-30° | 97.2 | 28.0 |
| 30°-40° | 70.6 | 20.3 |
| 40°-50° | 33.0 | 9.5 |
| 50°-60° | 11.1 | 3.2 |
| 60°-70° | 6.4 | 1.9 |
| 70°-80° | 3.4 | 1.0 |
| 80°-90° | 1.1 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 221.3 | 63.8 |
| 0°-40° | 291.9 | 84.1 |
| 0°-60° | 336.1 | 96.9 |
| 0°-90° | 347.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 347.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 402 | |
| 5° | 391 | 36 |
| 15° | 316 | 88 |
| 25° | 213 | 97 |
| 35° | 113 | 71 |
| 45° | 42 | 33 |
| 55° | 12 | 11 |
| 65° | 6 | 6 |
| 75° | 3 | 3 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1251395
CATALOG NUMBER: P3AS05R659030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 402.2 |
| 2.5° | 399.7 |
| 5° | 390.7 |
| 7.5° | 377.2 |
| 10° | 359.7 |
| 12.5° | 339.2 |
| 15° | 316.2 |
| 17.5° | 291.2 |
| 20° | 265.7 |
| 22.5° | 239.1 |
| 25° | 213.1 |
| 27.5° | 186.6 |
| 30° | 160.6 |
| 32.5° | 135.6 |
| 35° | 112.6 |
| 37.5° | 91.6 |
| 40° | 72.5 |
| 42.5° | 55.5 |
| 45° | 41.5 |
| 47.5° | 30.0 |
| 50° | 20.5 |
| 52.5° | 14.0 |
| 55° | 11.5 |
| 57.5° | 10.0 |
| 60° | 8.5 |
| 62.5° | 7.5 |
| 65° | 6.5 |
| 67.5° | 5.5 |
| 70° | 4.5 |
| 72.5° | 4.0 |
| 75° | 3.0 |
| 77.5° | 2.5 |
| 80° | 2.0 |
| 82.5° | 1.5 |
| 85° | 1.0 |
| 87.5° | 0.5 |
| 90° | 0.0 |

(END OF REPORT)