

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252395

Luminaire Tested: P3AS17R409030DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1803.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252395

CATALOG NUMBER: P3AS17R409030DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252395

CATALOG NUMBER: P3AS17R409030DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	919027
5°	912390
10°	888516
15°	793694
20°	526259
25°	197165
30°	52742
35°	20612
40°	7414
45°	3535
50°	1092
55°	497
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3535 cd/sqm

TEST NUMBER: P1252395

CATALOG NUMBER: P3AS17R409030DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	21.7
10°-20°	926.4	51.4
20°-30°	420.1	23.3
30°-40°	54.5	3.0
40°-50°	9.4	0.5
50°-60°	1.1	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1737.6	96.4
0°-40°	1792.1	99.4
0°-60°	1802.6	100.0
0°-90°	1803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1803.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4191	
5°	4145	391
15°	3496	926
25°	815	420
35°	77	54
45°	11	9
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252395

CATALOG NUMBER: P3AS17R409030DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4191.1
1°	4188.6
2°	4182.3
3°	4172.8
4°	4160.8
5°	4145.0
6°	4126.7
7°	4104.0
8°	4076.2
9°	4038.4
10°	3990.4
11°	3934.2
12°	3859.1
13°	3766.3
14°	3645.1
15°	3496.2
16°	3306.2
17°	3089.7
18°	2829.6
19°	2555.1
20°	2255.2
21°	1955.4
22°	1660.0
23°	1365.9
24°	1076.8
25°	814.9
26°	603.4
27°	441.8
28°	332.0
29°	258.2
30°	208.3
31°	172.3
32°	143.9
32.5°	131.3
33°	118.7
34°	96.6
35°	77.0
36°	60.6
37°	48.0
37.5°	42.9
38°	37.9
39°	31.6
40°	25.9
42.5°	17.0
45°	11.4



TEST NUMBER: P1252395

CATALOG NUMBER: P3AS17R409030DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.9
50°	3.2
52.5°	1.3
55°	1.3
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)