

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251447

Luminaire Tested: P3AS09R109030DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109030DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 354.0 lumens
Efficiency: N/A
Efficacy: 28.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251447
CATALOG NUMBER: P3AS09R109030DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1251447
 CATALOG NUMBER: P3AS09R109030DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152663
5°	141096
10°	112645
15°	85086
20°	64802
25°	49382
30°	35373
35°	23075
40°	14141
45°	8559
50°	5697
55°	4396
60°	3772
65°	3269
70°	2949
75°	2881
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8559 cd/sqm



TEST NUMBER: P1251447
 CATALOG NUMBER: P3AS09R109030DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	16.0
10°-20°	104.8	29.6
20°-30°	93.3	26.4
30°-40°	55.2	15.6
40°-50°	22.7	6.4
50°-60°	10.6	3.0
60°-70°	6.5	1.8
70°-80°	3.4	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.8	72.0
0°-40°	310.0	87.6
0°-60°	343.3	97.0
0°-90°	354.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	354.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	696	
5°	641	57
15°	375	105
25°	204	93
35°	86	55
45°	28	23
55°	12	11
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1251447
CATALOG NUMBER: P3AS09R109030DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	696.2
1°	694.4
2°	689.3
3°	678.9
4°	661.7
5°	641.0
6°	618.5
7°	592.1
8°	564.5
9°	536.3
10°	505.9
12.5°	436.3
15°	374.8
17.5°	321.9
20°	277.7
22.5°	238.6
25°	204.1
27.5°	170.7
30°	139.7
32.5°	111.5
35°	86.2
37.5°	66.1
40°	49.4
42.5°	36.8
45°	27.6
47.5°	21.3
50°	16.7
52.5°	13.8
55°	11.5
57.5°	9.8
60°	8.6
62.5°	7.5
65°	6.3
67.5°	5.7
70°	4.6
72.5°	4.0
75°	3.4
77.5°	2.3
80°	1.7
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)