

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251465

Luminaire Tested: P3AS09R159030DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159030DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 759.0 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251465
CATALOG NUMBER: P3AS09R159030DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1251465
 CATALOG NUMBER: P3AS09R159030DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	96	94	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	92	90	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	89	87	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	81	86	83	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	83	80	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	81	78	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	73	78	75	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	76	73	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	74	70	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	648391
5°	575543
10°	399681
15°	236369
20°	134622
25°	76964
30°	42589
35°	22700
40°	12566
45°	6791
50°	4230
55°	3364
60°	2895
65°	2646
70°	2372
75°	2457
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6791 cd/sqm



TEST NUMBER: P1251465
 CATALOG NUMBER: P3AS09R159030DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.3	29.3
10°-20°	293.4	38.7
20°-30°	151.1	19.9
30°-40°	56.7	7.5
40°-50°	18.6	2.4
50°-60°	8.0	1.1
60°-70°	5.1	0.7
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	666.9	87.9
0°-40°	723.6	95.3
0°-60°	750.2	98.8
0°-90°	759.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	759.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2957	
5°	2615	222
15°	1041	293
25°	318	151
35°	85	57
45°	22	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1251465
CATALOG NUMBER: P3AS09R159030DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2956.9
1°	2951.0
2°	2912.3
3°	2838.4
4°	2741.2
5°	2614.7
6°	2471.4
7°	2314.2
8°	2139.4
9°	1966.9
10°	1795.0
12.5°	1381.2
15°	1041.2
17.5°	779.4
20°	576.9
22.5°	430.7
25°	318.1
27.5°	231.8
30°	168.2
32.5°	119.2
35°	84.8
37.5°	60.7
40°	43.9
42.5°	31.4
45°	21.9
47.5°	16.1
50°	12.4
52.5°	10.2
55°	8.8
57.5°	7.3
60°	6.6
62.5°	5.8
65°	5.1
67.5°	4.4
70°	3.7
72.5°	3.7
75°	2.9
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)