

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251488

Luminaire Tested: P3AS09R209030DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209030DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 924.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251488

CATALOG NUMBER: P3AS09R209030DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1251488

CATALOG NUMBER: P3AS09R209030DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	110		113	112	110	109		108	106	105		104	103	102		101	100	99
2	112	109	107	104		110	108	105	103		104	103	101		102	100	99		99	98	97
3	109	105	102	100		108	104	101	99		102	99	97		99	98	96		97	96	95
4	107	102	99	96		105	101	98	96		99	97	95		97	95	93		96	94	92
5	104	99	96	93		103	98	95	93		97	94	92		95	93	91		94	92	91
6	102	97	93	91		101	96	93	90		95	92	90		94	91	89		93	90	89
7	100	94	91	88		99	94	91	88		93	90	88		92	89	87		91	89	87
8	98	92	89	86		97	92	89	86		91	88	86		90	88	86		89	87	85
9	96	90	87	85		95	90	87	85		89	86	84		89	86	84		88	86	84
10	94	89	85	83		93	88	85	83		88	85	83		87	84	83		87	84	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1435082
5°	1245605
10°	769636
15°	267311
20°	82094
25°	29010
30°	10736
35°	4310
40°	2290
45°	899
50°	512
55°	573
60°	658
65°	363
70°	449
75°	593
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 899 cd/sqm

TEST NUMBER: P1251488

CATALOG NUMBER: P3AS09R209030DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	469.6	50.8
10°-20°	372.6	40.3
20°-30°	64.5	7.0
30°-40°	11.7	1.3
40°-50°	2.7	0.3
50°-60°	1.3	0.1
60°-70°	0.8	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.8	98.1
0°-40°	918.5	99.4
0°-60°	922.5	99.8
0°-90°	924.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	924.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6544	
5°	5659	470
15°	1178	373
25°	120	65
35°	16	12
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1251488

CATALOG NUMBER: P3AS09R209030DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6544.5
1°	6513.0
2°	6388.7
3°	6189.0
4°	5955.0
5°	5658.8
6°	5319.4
7°	4924.4
8°	4474.6
9°	3969.3
10°	3456.5
12.5°	2180.3
15°	1177.5
17.5°	629.0
20°	351.8
22.5°	201.1
25°	119.9
27.5°	73.1
30°	42.4
32.5°	24.9
35°	16.1
37.5°	11.0
40°	8.0
42.5°	5.1
45°	2.9
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)