

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252494

Luminaire Tested: P3AS17R559030DE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252494  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R559030DE010 E3DLP1MW  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 937.0 lumens  
Efficiency: N/A  
Efficacy: 44.2 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252494  
CATALOG NUMBER: P3AS17R559030DE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1252494  
 CATALOG NUMBER: P3AS17R559030DE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92				92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79				79
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67				67
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55				55
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52				52
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49				49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	254892
5°	248492
10°	231013
15°	205722
20°	174829
25°	141081
30°	107561
35°	76506
40°	50495
45°	29926
50°	17569
55°	10819
60°	9604
65°	8665
70°	7437
75°	6524
80°	6440
85°	6542

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29926 cd/sqm



TEST NUMBER: P1252494  
 CATALOG NUMBER: P3AS17R559030DE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.8	11.2
10°-20°	251.2	26.8
20°-30°	266.1	28.4
30°-40°	179.8	19.2
40°-50°	78.8	8.4
50°-60°	28.2	3.0
60°-70°	16.5	1.8
70°-80°	8.6	0.9
80°-90°	2.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.1	66.4
0°-40°	802.0	85.6
0°-60°	909.0	97.0
0°-90°	937.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	937.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1162	
5°	1129	105
15°	906	251
25°	583	266
35°	286	180
45°	96	79
55°	28	28
65°	17	17
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P1252494  
CATALOG NUMBER: P3AS17R559030DE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1162.4
2.5°	1153.4
5°	1128.9
7.5°	1089.0
10°	1037.5
12.5°	975.8
15°	906.2
17.5°	829.0
20°	749.2
22.5°	665.5
25°	583.1
27.5°	502.0
30°	424.8
32.5°	351.4
35°	285.8
37.5°	226.6
40°	176.4
42.5°	132.6
45°	96.5
47.5°	70.8
50°	51.5
52.5°	36.0
55°	28.3
57.5°	25.7
60°	21.9
62.5°	19.3
65°	16.7
67.5°	14.2
70°	11.6
72.5°	10.3
75°	7.7
77.5°	6.4
80°	5.1
82.5°	3.9
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)