

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251509

Luminaire Tested: P3AS09R209030DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209030DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 358.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251509
CATALOG NUMBER: P3AS09R209030DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1251509
 CATALOG NUMBER: P3AS09R209030DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90				90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81				81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74				74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68				68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63				63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55				55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127314
5°	118754
10°	98529
15°	75347
20°	56542
25°	42583
30°	31473
35°	22004
40°	15085
45°	10451
50°	8972
55°	8869
60°	9254
65°	9288
70°	9489
75°	9828
80°	10607
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 12432 cd/sqm



TEST NUMBER: P1251509
 CATALOG NUMBER: P3AS09R209030DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.3	13.5
10°-20°	92.3	25.8
20°-30°	81.2	22.7
30°-40°	52.4	14.6
40°-50°	27.8	7.8
50°-60°	20.9	5.8
60°-70°	17.8	5.0
70°-80°	12.5	3.5
80°-90°	4.9	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.8	62.0
0°-40°	274.2	76.6
0°-60°	322.8	90.2
0°-90°	358.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	358.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	540	48
15°	332	92
25°	176	81
35°	82	52
45°	34	28
55°	23	21
65°	18	18
75°	12	13
85°	4	5
90°	0	



TEST NUMBER: P1251509
CATALOG NUMBER: P3AS09R209030DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	580.6
2.5°	569.0
5°	539.5
7.5°	494.2
10°	442.5
12.5°	385.6
15°	331.9
17.5°	283.4
20°	242.3
22.5°	207.6
25°	176.0
27.5°	148.6
30°	124.3
32.5°	102.2
35°	82.2
37.5°	66.4
40°	52.7
42.5°	42.1
45°	33.7
47.5°	29.5
50°	26.3
52.5°	24.2
55°	23.2
57.5°	22.1
60°	21.1
62.5°	19.0
65°	17.9
67.5°	16.9
70°	14.8
72.5°	13.7
75°	11.6
77.5°	10.5
80°	8.4
82.5°	7.4
85°	4.2
87.5°	2.1
90°	0.0

(END OF REPORT)