

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252530

Luminaire Tested: P3AS17R659030DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659030DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1592.0 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252530

CATALOG NUMBER: P3AS17R659030DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1252530

CATALOG NUMBER: P3AS17R659030DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	389048
5°	366167
10°	361516
15°	355121
20°	335306
25°	311195
30°	241885
35°	139923
40°	56391
45°	25956
50°	10098
55°	3938
60°	3377
65°	3321
70°	3334
75°	3304
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25956 cd/sqm

TEST NUMBER: P1252530

CATALOG NUMBER: P3AS17R659030DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.1	9.9
10°-20°	436.8	27.4
20°-30°	571.8	35.9
30°-40°	331.2	20.8
40°-50°	70.9	4.5
50°-60°	11.5	0.7
60°-70°	6.4	0.4
70°-80°	3.8	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1166.8	73.3
0°-40°	1498.0	94.1
0°-60°	1580.5	99.3
0°-90°	1592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1592.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1774	
5°	1664	158
15°	1564	437
25°	1286	572
35°	523	331
45°	84	71
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1252530

CATALOG NUMBER: P3AS17R659030DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1774.2
2.5°	1724.0
5°	1663.5
7.5°	1639.0
10°	1623.6
12.5°	1601.7
15°	1564.3
17.5°	1506.4
20°	1436.9
22.5°	1371.2
25°	1286.2
27.5°	1143.3
30°	955.3
32.5°	740.3
35°	522.7
37.5°	330.9
40°	197.0
42.5°	123.6
45°	83.7
47.5°	54.1
50°	29.6
52.5°	14.2
55°	10.3
57.5°	9.0
60°	7.7
62.5°	7.7
65°	6.4
67.5°	5.2
70°	5.2
72.5°	3.9
75°	3.9
77.5°	2.6
80°	2.6
82.5°	1.3
85°	1.3
87.5°	1.3
90°	0.0

(END OF REPORT)