

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251570

Luminaire Tested: P3AS09R309030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 472.0 lumens
Efficiency: N/A
Efficacy: 42.5 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251570

CATALOG NUMBER: P3AS09R309030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251570

CATALOG NUMBER: P3AS09R309030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161281
5°	156262
10°	140812
15°	116482
20°	90168
25°	67649
30°	49121
35°	32712
40°	20123
45°	11815
50°	7232
55°	5887
60°	5131
65°	4203
70°	3783
75°	3728
80°	2778
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11815 cd/sqm

TEST NUMBER: P1251570

CATALOG NUMBER: P3AS09R309030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	13.8
10°-20°	141.3	29.9
20°-30°	128.5	27.2
30°-40°	77.7	16.5
40°-50°	31.2	6.6
50°-60°	13.8	2.9
60°-70°	8.3	1.8
70°-80°	4.5	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.2	71.0
0°-40°	412.9	87.5
0°-60°	457.8	97.0
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	736	
5°	710	65
15°	513	141
25°	280	129
35°	122	78
45°	38	31
55°	15	14
65°	8	8
75°	4	5
85°	2	1
90°	0	

TEST NUMBER: P1251570

CATALOG NUMBER: P3AS09R309030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	735.5
1°	734.8
2°	731.9
3°	726.8
4°	719.4
5°	709.9
6°	698.2
7°	685.8
8°	669.7
9°	651.4
10°	632.4
11°	610.4
12°	587.0
13°	563.6
14°	537.9
15°	513.1
17.5°	447.9
20°	386.4
22.5°	329.3
25°	279.6
27.5°	234.2
30°	194.0
32.5°	156.6
35°	122.2
37.5°	93.7
40°	70.3
42.5°	51.2
45°	38.1
47.5°	28.5
50°	21.2
52.5°	16.8
55°	15.4
57.5°	13.2
60°	11.7
62.5°	9.5
65°	8.1
67.5°	7.3
70°	5.9
72.5°	5.1
75°	4.4
77.5°	3.7
80°	2.2
82.5°	1.5
85°	1.5
87.5°	0.7



TEST NUMBER: P1251570

CATALOG NUMBER: P3AS09R309030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)