

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252546

Luminaire Tested: P3AS17R659030DE010 E3DLD1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1252546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R659030DE010 E3DLD1MW  
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1014.0 lumens  
Efficiency: N/A  
Efficacy: 47.8 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1252546  
CATALOG NUMBER: P3AS17R659030DE010 E3DLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1252546  
 CATALOG NUMBER: P3AS17R659030DE010 E3DLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	180446
5°	178010
10°	172052
15°	162248
20°	149650
25°	135855
30°	120322
35°	102392
40°	81467
45°	57494
50°	33398
55°	18198
60°	16928
65°	15358
70°	14041
75°	13132
80°	11365
85°	9812

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 57494 cd/sqm



TEST NUMBER: P1252546  
 CATALOG NUMBER: P3AS17R659030DE010 E3DLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.1	7.5
10°-20°	200.0	19.7
20°-30°	257.0	25.3
30°-40°	237.7	23.4
40°-50°	143.5	14.2
50°-60°	48.9	4.8
60°-70°	29.5	2.9
70°-80°	16.7	1.6
80°-90°	4.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.0	52.6
0°-40°	770.7	76.0
0°-60°	963.2	95.0
0°-90°	1014.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1014.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	823	
5°	809	76
15°	715	200
25°	562	257
35°	382	238
45°	185	144
55°	48	49
65°	30	29
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P1252546  
CATALOG NUMBER: P3AS17R659030DE010 E3DLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	822.9
2.5°	819.0
5°	808.7
7.5°	793.3
10°	772.7
12.5°	746.9
15°	714.7
17.5°	680.0
20°	641.3
22.5°	601.4
25°	561.5
27.5°	519.0
30°	475.2
32.5°	431.4
35°	382.5
37.5°	334.8
40°	284.6
42.5°	234.4
45°	185.4
47.5°	140.4
50°	97.9
52.5°	61.8
55°	47.6
57.5°	42.5
60°	38.6
62.5°	33.5
65°	29.6
67.5°	25.8
70°	21.9
72.5°	19.3
75°	15.5
77.5°	12.9
80°	9.0
82.5°	6.4
85°	3.9
87.5°	2.6
90°	0.0

(END OF REPORT)