

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252549

Luminaire Tested: P3AS17R659030DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659030DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 437.0 lumens
Efficiency: N/A
Efficacy: 20.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252549
CATALOG NUMBER: P3AS17R659030DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1252549
 CATALOG NUMBER: P3AS17R659030DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111088
5°	108320
10°	100867
15°	90398
20°	78080
25°	64939
30°	51198
35°	37959
40°	26163
45°	16219
50°	8801
55°	5543
60°	4693
65°	4255
70°	3654
75°	3219
80°	3157
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16219 cd/sqm



TEST NUMBER: P1252549
 CATALOG NUMBER: P3AS17R659030DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.7	10.5
10°-20°	110.7	25.3
20°-30°	122.4	28.0
30°-40°	88.9	20.3
40°-50°	41.6	9.5
50°-60°	14.0	3.2
60°-70°	8.1	1.9
70°-80°	4.2	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.8	63.8
0°-40°	367.6	84.1
0°-60°	423.3	96.9
0°-90°	437.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	437.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	507	
5°	492	46
15°	398	111
25°	268	122
35°	142	89
45°	52	42
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1252549
CATALOG NUMBER: P3AS17R659030DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	506.6
2.5°	503.4
5°	492.1
7.5°	475.1
10°	453.0
12.5°	427.2
15°	398.2
17.5°	366.7
20°	334.6
22.5°	301.2
25°	268.4
27.5°	235.0
30°	202.2
32.5°	170.7
35°	141.8
37.5°	115.3
40°	91.4
42.5°	69.9
45°	52.3
47.5°	37.8
50°	25.8
52.5°	17.6
55°	14.5
57.5°	12.6
60°	10.7
62.5°	9.5
65°	8.2
67.5°	6.9
70°	5.7
72.5°	5.0
75°	3.8
77.5°	3.2
80°	2.5
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)