

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252550

Luminaire Tested: P3AS17R659030DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659030DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 892.0 lumens
Efficiency: N/A
Efficacy: 42.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252550
CATALOG NUMBER: P3AS17R659030DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1252550
 CATALOG NUMBER: P3AS17R659030DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226736
5°	221087
10°	205897
15°	184519
20°	159357
25°	132564
30°	104522
35°	77470
40°	53386
45°	33089
50°	17978
55°	11316
60°	9604
65°	8665
70°	7437
75°	6524
80°	6440
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33089 cd/sqm



TEST NUMBER: P1252550
 CATALOG NUMBER: P3AS17R659030DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.3	10.5
10°-20°	225.9	25.3
20°-30°	249.8	28.0
30°-40°	181.4	20.3
40°-50°	85.0	9.5
50°-60°	28.6	3.2
60°-70°	16.5	1.9
70°-80°	8.6	1.0
80°-90°	2.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	569.0	63.8
0°-40°	750.4	84.1
0°-60°	864.0	96.9
0°-90°	892.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	892.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1034	
5°	1004	93
15°	813	226
25°	548	250
35°	289	181
45°	107	85
55°	30	29
65°	17	17
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P1252550
CATALOG NUMBER: P3AS17R659030DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1034.0
2.5°	1027.5
5°	1004.4
7.5°	969.7
10°	924.7
12.5°	871.9
15°	812.8
17.5°	748.5
20°	682.9
22.5°	614.7
25°	547.9
27.5°	479.7
30°	412.8
32.5°	348.5
35°	289.4
37.5°	235.3
40°	186.5
42.5°	142.8
45°	106.7
47.5°	77.2
50°	52.7
52.5°	36.0
55°	29.6
57.5°	25.7
60°	21.9
62.5°	19.3
65°	16.7
67.5°	14.1
70°	11.6
72.5°	10.3
75°	7.7
77.5°	6.4
80°	5.1
82.5°	3.9
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)