

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251577

Luminaire Tested: P3AS09R359030DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 929.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251577

CATALOG NUMBER: P3AS09R359030DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1251577

CATALOG NUMBER: P3AS09R359030DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	103	100		102	100	98		99	98	96		97	95	94
3	107	102	98	95		105	101	97	95		98	96	93		96	94	92		94	92	90
4	104	98	94	91		102	97	93	90		95	92	89		93	90	88		91	89	87
5	100	94	90	87		99	93	89	86		92	88	86		90	87	85		89	86	84
6	97	91	86	83		96	90	86	83		89	85	82		87	84	82		86	83	81
7	94	87	83	80		93	87	83	80		86	82	79		85	81	79		84	81	79
8	91	84	80	77		90	84	80	77		83	79	77		82	79	76		81	78	76
9	89	82	77	74		88	81	77	74		80	77	74		80	76	74		79	76	74
10	86	79	75	72		85	79	75	72		78	74	72		77	74	72		77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	605763
5°	593439
10°	552072
15°	404747
20°	207265
25°	74690
30°	29093
35°	10172
40°	4179
45°	1147
50°	989
55°	1109
60°	965
65°	778
70°	962
75°	1271
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 1271 cd/sqm

TEST NUMBER: P1251577

CATALOG NUMBER: P3AS09R359030DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.3	27.1
10°-20°	471.6	50.8
20°-30°	167.0	18.0
30°-40°	29.2	3.1
40°-50°	4.3	0.5
50°-60°	2.4	0.3
60°-70°	1.7	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.9	95.8
0°-40°	919.1	98.9
0°-60°	925.7	99.6
0°-90°	929.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2762	
5°	2696	251
15°	1783	472
25°	309	167
35°	38	29
45°	4	4
55°	3	2
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1251577

CATALOG NUMBER: P3AS09R359030DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2762.5
1°	2761.8
2°	2753.0
3°	2736.2
4°	2720.8
5°	2696.0
6°	2670.3
7°	2641.8
8°	2606.7
9°	2551.8
10°	2479.4
11°	2379.2
12°	2258.5
13°	2115.1
14°	1957.0
15°	1782.9
17.5°	1327.9
20°	888.2
22.5°	535.5
25°	308.7
27.5°	184.4
30°	114.9
32.5°	66.6
35°	38.0
37.5°	24.1
40°	14.6
42.5°	7.3
45°	3.7
47.5°	2.9
50°	2.9
52.5°	2.9
55°	2.9
57.5°	2.2
60°	2.2
62.5°	2.2
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1251577

CATALOG NUMBER: P3AS09R359030DE010 E3CD1MB

CANDELA DISTRIBUTION (continued):



(END OF REPORT)