

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252553

Luminaire Tested: P3AS17R659030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1291.0 lumens
Efficiency: N/A
Efficacy: 60.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252553

CATALOG NUMBER: P3AS17R659030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1252553

CATALOG NUMBER: P3AS17R659030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	304449
5°	300814
10°	289373
15°	271080
20°	243831
25°	207036
30°	161924
35°	115402
40°	75513
45°	46703
50°	23709
55°	8372
60°	7324
65°	7368
70°	6604
75°	6524
80°	6440
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 46703 cd/sqm

TEST NUMBER: P1252553

CATALOG NUMBER: P3AS17R659030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	9.9
10°-20°	332.3	25.7
20°-30°	388.4	30.1
30°-40°	271.4	21.0
40°-50°	119.5	9.3
50°-60°	26.6	2.1
60°-70°	13.5	1.0
70°-80°	8.1	0.6
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.0	65.8
0°-40°	1120.5	86.8
0°-60°	1266.5	98.1
0°-90°	1291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1388	
5°	1367	128
15°	1194	332
25°	856	388
35°	431	271
45°	151	119
55°	22	27
65°	14	14
75°	8	8
85°	3	3
90°	0	

TEST NUMBER: P1252553

CATALOG NUMBER: P3AS17R659030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1388.4
2.5°	1383.3
5°	1366.6
7.5°	1338.2
10°	1299.6
12.5°	1252.0
15°	1194.1
17.5°	1123.4
20°	1044.9
22.5°	956.1
25°	855.7
27.5°	750.2
30°	639.5
32.5°	532.7
35°	431.1
37.5°	342.3
40°	263.8
42.5°	199.4
45°	150.6
47.5°	110.7
50°	69.5
52.5°	36.0
55°	21.9
57.5°	19.3
60°	16.7
62.5°	15.4
65°	14.2
67.5°	11.6
70°	10.3
72.5°	9.0
75°	7.7
77.5°	6.4
80°	5.1
82.5°	3.9
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)