

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251612

Luminaire Tested: P3AS09R409030DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409030DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1024.0 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251612

CATALOG NUMBER: P3AS09R409030DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251612

CATALOG NUMBER: P3AS09R409030DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521954
5°	518180
10°	504622
15°	450763
20°	298903
25°	111974
30°	29954
35°	11698
40°	4208
45°	2016
50°	614
55°	268
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2016 cd/sqm

TEST NUMBER: P1251612

CATALOG NUMBER: P3AS09R409030DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.2	21.7
10°-20°	526.1	51.4
20°-30°	238.6	23.3
30°-40°	30.9	3.0
40°-50°	5.4	0.5
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	986.9	96.4
0°-40°	1017.8	99.4
0°-60°	1023.8	100.0
0°-90°	1024.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1024.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2380	
5°	2354	222
15°	1986	526
25°	463	239
35°	44	31
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1251612

CATALOG NUMBER: P3AS09R409030DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2380.3
1°	2378.9
2°	2375.3
3°	2369.9
4°	2363.1
5°	2354.1
6°	2343.7
7°	2330.8
8°	2315.1
9°	2293.6
10°	2266.3
11°	2234.4
12°	2191.8
13°	2139.1
14°	2070.2
15°	1985.6
16°	1877.7
17°	1754.8
18°	1607.1
19°	1451.1
20°	1280.9
21°	1110.6
22°	942.8
23°	775.8
24°	611.6
25°	462.8
26°	342.7
27°	250.9
28°	188.6
29°	146.6
30°	118.3
31°	97.9
32°	81.7
32.5°	74.6
33°	67.4
34°	54.8
35°	43.7
36°	34.4
37°	27.2
37.5°	24.4
38°	21.5
39°	17.9
40°	14.7
42.5°	9.7
45°	6.5



TEST NUMBER: P1251612

CATALOG NUMBER: P3AS09R409030DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	3.9
50°	1.8
52.5°	0.7
55°	0.7
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)