

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251621

Luminaire Tested: P3AS09R409030DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409030DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 654.0 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251621
CATALOG NUMBER: P3AS09R409030DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1251621
 CATALOG NUMBER: P3AS09R409030DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146808
5°	144155
10°	135869
15°	123429
20°	108416
25°	92594
30°	76695
35°	59160
40°	42107
45°	28375
50°	15488
55°	10896
60°	10262
65°	9495
70°	8463
75°	8049
80°	6440
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28375 cd/sqm



TEST NUMBER: P1251621
 CATALOG NUMBER: P3AS09R409030DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	9.3
10°-20°	151.4	23.2
20°-30°	175.1	26.8
30°-40°	138.0	21.1
40°-50°	70.8	10.8
50°-60°	27.1	4.1
60°-70°	17.9	2.7
70°-80°	9.7	1.5
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.6	59.3
0°-40°	525.6	80.4
0°-60°	623.5	95.3
0°-90°	654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	654.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	670	
5°	655	61
15°	544	151
25°	383	175
35°	221	138
45°	92	71
55°	28	27
65°	18	18
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1251621
CATALOG NUMBER: P3AS09R409030DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	669.5
2.5°	665.8
5°	654.9
7.5°	635.8
10°	610.2
12.5°	580.2
15°	543.7
17.5°	505.6
20°	464.6
22.5°	422.9
25°	382.7
27.5°	342.4
30°	302.9
32.5°	262.7
35°	221.0
37.5°	182.2
40°	147.1
42.5°	117.1
45°	91.5
47.5°	66.6
50°	45.4
52.5°	32.9
55°	28.5
57.5°	25.6
60°	23.4
62.5°	20.5
65°	18.3
67.5°	15.4
70°	13.2
72.5°	11.0
75°	9.5
77.5°	7.3
80°	5.1
82.5°	4.4
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)