

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251629

Luminaire Tested: P3AS09R409030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 852.0 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251629

CATALOG NUMBER: P3AS09R409030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1251629

CATALOG NUMBER: P3AS09R409030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	377009
5°	366057
10°	332169
15°	274417
20°	197954
25°	122451
30°	66289
35°	34265
40°	18635
45°	10420
50°	5254
55°	3900
60°	3508
65°	3424
70°	3270
75°	3135
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10420 cd/sqm

TEST NUMBER: P1251629

CATALOG NUMBER: P3AS09R409030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.3	18.0
10°-20°	329.2	38.6
20°-30°	234.9	27.6
30°-40°	86.5	10.2
40°-50°	27.2	3.2
50°-60°	9.5	1.1
60°-70°	6.5	0.8
70°-80°	3.9	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	717.4	84.2
0°-40°	803.8	94.3
0°-60°	840.5	98.7
0°-90°	852.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	852.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1719	
5°	1663	153
15°	1209	329
25°	506	235
35°	128	86
45°	34	27
55°	10	9
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1251629

CATALOG NUMBER: P3AS09R409030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1719.3
2.5°	1706.1
5°	1663.0
7.5°	1591.3
10°	1491.8
12.5°	1365.3
15°	1208.8
17.5°	1033.3
20°	848.3
22.5°	666.2
25°	506.1
27.5°	371.5
30°	261.8
32.5°	183.6
35°	128.0
37.5°	90.7
40°	65.1
42.5°	46.8
45°	33.6
47.5°	22.7
50°	15.4
52.5°	11.0
55°	10.2
57.5°	9.5
60°	8.0
62.5°	7.3
65°	6.6
67.5°	5.9
70°	5.1
72.5°	4.4
75°	3.7
77.5°	2.9
80°	2.2
82.5°	1.5
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)