

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251649

Luminaire Tested: P3AS09R459030DE010 E3DLD1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251649  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R459030DE010 E3DLD1WMH  
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 635.0 lumens  
Efficiency: N/A  
Efficacy: 57.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251649  
CATALOG NUMBER: P3AS09R459030DE010 E3DLD1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1251649

CATALOG NUMBER: P3AS09R459030DE010 E3DLD1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134638
5°	132247
10°	125137
15°	114121
20°	100925
25°	87634
30°	75227
35°	62694
40°	46716
45°	28592
50°	13236
55°	10360
60°	9955
65°	9132
70°	8463
75°	8049
80°	7450
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 28592 cd/sqm



TEST NUMBER: P1251649

CATALOG NUMBER: P3AS09R459030DE010 E3DLD1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.1	8.8
10°-20°	140.0	22.0
20°-30°	166.3	26.2
30°-40°	144.5	22.8
40°-50°	72.5	11.4
50°-60°	25.2	4.0
60°-70°	17.7	2.8
70°-80°	9.8	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.4	57.1
0°-40°	506.9	79.8
0°-60°	604.5	95.2
0°-90°	635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	635.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	614	
5°	601	56
15°	503	140
25°	362	166
35°	234	145
45°	92	72
55°	27	25
65°	18	18
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1251649  
CATALOG NUMBER: P3AS09R459030DE010 E3DLD1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	614.0
2.5°	611.1
5°	600.8
7.5°	584.7
10°	562.0
12.5°	534.2
15°	502.7
17.5°	467.6
20°	432.5
22.5°	396.6
25°	362.2
27.5°	329.3
30°	297.1
32.5°	266.4
35°	234.2
37.5°	199.8
40°	163.2
42.5°	127.3
45°	92.2
47.5°	60.7
50°	38.8
52.5°	30.0
55°	27.1
57.5°	24.9
60°	22.7
62.5°	20.5
65°	17.6
67.5°	15.4
70°	13.2
72.5°	11.0
75°	9.5
77.5°	7.3
80°	5.9
82.5°	4.4
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)