

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251655

Luminaire Tested: P3AS09R459030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R459030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.0 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251655

CATALOG NUMBER: P3AS09R459030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251655

CATALOG NUMBER: P3AS09R459030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157268
5°	153687
10°	141770
15°	123270
20°	101275
25°	78803
30°	58186
35°	40957
40°	25562
45°	13831
50°	7505
55°	6423
60°	5789
65°	4929
70°	4231
75°	4321
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13831 cd/sqm

TEST NUMBER: P1251655

CATALOG NUMBER: P3AS09R459030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	12.2
10°-20°	150.1	28.4
20°-30°	149.0	28.2
30°-40°	96.0	18.2
40°-50°	37.0	7.0
50°-60°	15.0	2.8
60°-70°	9.5	1.8
70°-80°	5.1	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.8	68.9
0°-40°	459.8	87.1
0°-60°	511.8	96.9
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	717	
5°	698	65
15°	543	150
25°	326	149
35°	153	96
45°	45	37
55°	17	15
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1251655

CATALOG NUMBER: P3AS09R459030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	717.2
2.5°	713.6
5°	698.2
7.5°	671.8
10°	636.7
12.5°	592.8
15°	543.0
17.5°	488.9
20°	434.0
22.5°	378.4
25°	325.7
27.5°	275.9
30°	229.8
32.5°	189.5
35°	153.0
37.5°	120.0
40°	89.3
42.5°	64.4
45°	44.6
47.5°	30.0
50°	22.0
52.5°	18.3
55°	16.8
57.5°	14.6
60°	13.2
62.5°	11.0
65°	9.5
67.5°	8.1
70°	6.6
72.5°	5.9
75°	5.1
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)