

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251665

Luminaire Tested: P3AS09R509030DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509030DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1016.1 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251665

CATALOG NUMBER: P3AS09R509030DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1251665

CATALOG NUMBER: P3AS09R509030DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	68
8	84	76	71	67	83	76	71	67	74	70	67	74	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	355059
5°	345608
10°	329809
15°	298572
20°	258299
25°	211875
30°	121715
35°	37798
40°	10162
45°	3566
50°	853
55°	268
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3566 cd/sqm

TEST NUMBER: P1251665

CATALOG NUMBER: P3AS09R509030DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.1	14.5
10°-20°	364.4	35.9
20°-30°	383.0	37.7
30°-40°	109.6	10.8
40°-50°	10.7	1.1
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	894.5	88.0
0°-40°	1004.1	98.8
0°-60°	1015.7	100.0
0°-90°	1016.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1016.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1619	
5°	1570	147
15°	1315	364
25°	876	383
35°	141	110
45°	12	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1251665

CATALOG NUMBER: P3AS09R509030DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1619.2
1°	1616.7
2°	1609.5
3°	1599.1
4°	1585.1
5°	1570.1
6°	1553.9
7°	1536.7
8°	1520.6
9°	1501.9
10°	1481.2
11°	1457.1
12°	1429.5
13°	1395.1
14°	1357.8
15°	1315.2
16°	1270.0
17°	1226.3
18°	1181.5
19°	1142.1
20°	1106.9
21°	1073.2
22°	1034.9
23°	990.8
24°	939.2
25°	875.7
26°	806.9
27°	730.2
28°	653.8
29°	571.4
30°	480.7
31°	395.7
32°	317.6
32.5°	283.5
33°	249.1
34°	191.1
35°	141.2
36°	103.6
37°	77.1
37.5°	66.7
38°	57.7
39°	44.8
40°	35.5
42.5°	20.1
45°	11.5



TEST NUMBER: P1251665

CATALOG NUMBER: P3AS09R509030DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.5
50°	2.5
52.5°	1.1
55°	0.7
57.5°	0.7
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)