

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251670

Luminaire Tested: P3AS09R509030DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509030DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 823.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251670

CATALOG NUMBER: P3AS09R509030DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1251670

CATALOG NUMBER: P3AS09R509030DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95			94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78			76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73			72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69			67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65			64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61			60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58			57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55			54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	262018
5°	256746
10°	240499
15°	215279
20°	181176
25°	138274
30°	89862
35°	53271
40°	30801
45°	15443
50°	5731
55°	4473
60°	4166
65°	3788
70°	3783
75°	3728
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15443 cd/sqm

TEST NUMBER: P1251670

CATALOG NUMBER: P3AS09R509030DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	13.2
10°-20°	262.3	31.9
20°-30°	257.3	31.3
30°-40°	129.6	15.8
40°-50°	41.0	5.0
50°-60°	10.6	1.3
60°-70°	7.5	0.9
70°-80°	4.6	0.6
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.1	76.3
0°-40°	757.7	92.1
0°-60°	809.2	98.3
0°-90°	823.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	823.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1195	
5°	1166	109
15°	948	262
25°	572	257
35°	199	130
45°	50	41
55°	12	11
65°	7	8
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1251670

CATALOG NUMBER: P3AS09R509030DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1194.9
2.5°	1187.6
5°	1166.4
7.5°	1128.4
10°	1080.1
12.5°	1017.9
15°	948.3
17.5°	867.9
20°	776.4
22.5°	677.6
25°	571.5
27.5°	458.8
30°	354.9
32.5°	267.1
35°	199.0
37.5°	147.1
40°	107.6
42.5°	76.1
45°	49.8
47.5°	28.5
50°	16.8
52.5°	12.4
55°	11.7
57.5°	10.2
60°	9.5
62.5°	8.8
65°	7.3
67.5°	6.6
70°	5.9
72.5°	5.1
75°	4.4
77.5°	3.7
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)