

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252616

Luminaire Tested: P3AS20R209030D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209030D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2134.1 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252616

CATALOG NUMBER: P3AS20R209030D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1252616

CATALOG NUMBER: P3AS20R209030D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101
2	112	109	107	104	110	108	105	103	104	103	101		102	100	99		99
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97
4	107	102	99	96	105	101	98	96	99	97	95		97	95	93		96
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		93
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3314340
5°	2876726
10°	1777522
15°	617393
20°	189600
25°	67020
30°	24814
35°	9958
40°	5324
45°	2109
50°	1160
55°	1300
60°	1491
65°	882
70°	1090
75°	1440
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2109 cd/sqm

TEST NUMBER: P1252616

CATALOG NUMBER: P3AS20R209030D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1084.6	50.8
10°-20°	860.6	40.3
20°-30°	149.0	7.0
30°-40°	27.1	1.3
40°-50°	6.2	0.3
50°-60°	3.1	0.1
60°-70°	1.9	0.1
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2094.2	98.1
0°-40°	2121.3	99.4
0°-60°	2130.6	99.8
0°-90°	2134.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2134.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15115	
5°	13069	###
15°	2720	861
25°	277	149
35°	37	27
45°	7	6
55°	3	3
65°	2	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1252616

CATALOG NUMBER: P3AS20R209030D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	15114.6
1°	15042.0
2°	14754.8
3°	14293.7
4°	13753.2
5°	13069.0
6°	12285.3
7°	11373.1
8°	10334.3
9°	9167.1
10°	7983.0
12.5°	5035.4
15°	2719.6
17.5°	1452.7
20°	812.5
22.5°	464.5
25°	277.0
27.5°	168.9
30°	98.0
32.5°	57.4
35°	37.2
37.5°	25.3
40°	18.6
42.5°	11.8
45°	6.8
47.5°	3.4
50°	3.4
52.5°	3.4
55°	3.4
57.5°	3.4
60°	3.4
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	1.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)