

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251723

Luminaire Tested: P3AS09R609030DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1251723  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R609030DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 877.0 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1251723  
CATALOG NUMBER: P3AS09R609030DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1251723  
 CATALOG NUMBER: P3AS09R609030DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	229784
5°	216927
10°	211285
15°	206448
20°	191957
25°	171591
30°	131083
35°	75677
40°	29369
45°	12249
50°	2695
55°	421
60°	307
65°	208
70°	256
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12249 cd/sqm



TEST NUMBER: P1251723  
 CATALOG NUMBER: P3AS09R609030DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.0	10.6
10°-20°	253.3	28.9
20°-30°	317.3	36.2
30°-40°	177.4	20.2
40°-50°	33.7	3.8
50°-60°	1.7	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.6	75.7
0°-40°	841.0	95.9
0°-60°	876.5	99.9
0°-90°	877.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1048	
5°	986	93
15°	909	253
25°	709	317
35°	283	177
45°	40	34
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1251723  
CATALOG NUMBER: P3AS09R609030DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1047.9
1°	1043.6
2°	1030.0
3°	1013.8
4°	998.8
5°	985.5
6°	975.4
7°	966.8
8°	960.4
9°	954.3
10°	948.9
11°	943.5
12°	937.4
13°	929.9
14°	920.9
15°	909.4
16°	895.4
17°	879.7
18°	861.7
19°	841.3
20°	822.6
21°	802.5
22°	781.7
23°	759.8
24°	735.8
25°	709.2
26°	678.0
27°	643.2
28°	604.1
29°	562.5
30°	517.7
31°	472.5
32°	425.8
32.5°	400.4
33°	377.4
34°	329.7
35°	282.7
36°	240.4
37°	195.5
37.5°	175.1
38°	155.0
39°	124.8
40°	102.6
42.5°	62.4
45°	39.5



TEST NUMBER: P1251723  
CATALOG NUMBER: P3AS09R609030DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	21.9
50°	7.9
52.5°	1.8
55°	1.1
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)