

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252648

Luminaire Tested: P3AS20R259030D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259030D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2284.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252648

CATALOG NUMBER: P3AS20R259030D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252648

CATALOG NUMBER: P3AS20R259030D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		97
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		94
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		92
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		89
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		87
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		85
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		83
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		81
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		79
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2501400
5°	2317185
10°	1792841
15°	856327
20°	282335
25°	119015
30°	46134
35°	19943
40°	6641
45°	3070
50°	1126
55°	650
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3070 cd/sqm

TEST NUMBER: P1252648

CATALOG NUMBER: P3AS20R259030D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	925.3	40.5
10°-20°	1052.4	46.1
20°-30°	244.6	10.7
30°-40°	51.3	2.2
40°-50°	8.3	0.4
50°-60°	1.4	0.1
60°-70°	0.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2222.3	97.3
0°-40°	2273.6	99.5
0°-60°	2283.3	100.0
0°-90°	2284.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2284.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11407	
5°	10527	925
15°	3772	1052
25°	492	245
35°	74	51
45°	10	8
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252648

CATALOG NUMBER: P3AS20R259030D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	11407.3
1°	11384.1
2°	11265.7
3°	11099.3
4°	10845.0
5°	10527.0
6°	10118.8
7°	9691.5
8°	9212.0
9°	8671.2
10°	8051.8
11°	7333.8
12°	6509.8
13°	5607.2
14°	4663.1
15°	3772.1
16°	2983.7
17°	2324.5
18°	1828.5
19°	1462.5
20°	1209.9
21°	1011.1
22°	848.8
23°	708.9
24°	592.9
25°	491.9
27.5°	291.5
30°	182.2
32.5°	116.8
35°	74.5
37.5°	44.7
40°	23.2
42.5°	14.9
45°	9.9
47.5°	5.8
50°	3.3
52.5°	1.7
55°	1.7
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.0
72.5°	0.0



TEST NUMBER: P1252648

CATALOG NUMBER: P3AS20R259030D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)