

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251766

Luminaire Tested: P3AS09R659030DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659030DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 249.0 lumens
Efficiency: N/A
Efficacy: 22.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251766
CATALOG NUMBER: P3AS09R659030DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1251766
 CATALOG NUMBER: P3AS09R659030DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	63	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63284
5°	61721
10°	57469
15°	51510
20°	44477
25°	36994
30°	29169
35°	21630
40°	14914
45°	9241
50°	5015
55°	3173
60°	2675
65°	2439
70°	2052
75°	1864
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9241 cd/sqm



TEST NUMBER: P1251766
 CATALOG NUMBER: P3AS09R659030DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.1	10.5
10°-20°	63.0	25.3
20°-30°	69.7	28.0
30°-40°	50.7	20.3
40°-50°	23.7	9.5
50°-60°	8.0	3.2
60°-70°	4.6	1.9
70°-80°	2.4	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.8	63.8
0°-40°	209.5	84.1
0°-60°	241.2	96.9
0°-90°	249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	289	
5°	280	26
15°	227	63
25°	153	70
35°	81	51
45°	30	24
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1251766
CATALOG NUMBER: P3AS09R659030DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	288.6
2.5°	286.8
5°	280.4
7.5°	270.7
10°	258.1
12.5°	243.4
15°	226.9
17.5°	208.9
20°	190.6
22.5°	171.6
25°	152.9
27.5°	133.9
30°	115.2
32.5°	97.3
35°	80.8
37.5°	65.7
40°	52.1
42.5°	39.8
45°	29.8
47.5°	21.5
50°	14.7
52.5°	10.1
55°	8.3
57.5°	7.2
60°	6.1
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.2
72.5°	2.9
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)