

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252660

Luminaire Tested: P3AS20R259030D010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259030D010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1357.0 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252660

CATALOG NUMBER: P3AS20R259030D010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1252660

CATALOG NUMBER: P3AS20R259030D010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322518
5°	314813
10°	291734
15°	259820
20°	223273
25°	189785
30°	156227
35°	121746
40°	87593
45°	55572
50°	32886
55°	22632
60°	20744
65°	19302
70°	17311
75°	15759
80°	14901
85°	12831

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 55572 cd/sqm

TEST NUMBER: P1252660

CATALOG NUMBER: P3AS20R259030D010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.6	9.8
10°-20°	317.7	23.4
20°-30°	359.0	26.5
30°-40°	284.0	20.9
40°-50°	143.5	10.6
50°-60°	57.5	4.2
60°-70°	36.8	2.7
70°-80°	20.3	1.5
80°-90°	5.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.3	59.6
0°-40°	1093.3	80.6
0°-60°	1294.2	95.4
0°-90°	1357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1471	
5°	1430	133
15°	1144	318
25°	784	359
35°	455	284
45°	179	143
55°	59	57
65°	37	37
75°	19	20
85°	5	6
90°	0	

TEST NUMBER: P1252660

CATALOG NUMBER: P3AS20R259030D010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1470.8
1°	1470.8
2°	1465.7
3°	1457.2
4°	1445.4
5°	1430.2
6°	1411.6
7°	1389.6
8°	1366.0
9°	1338.9
10°	1310.2
11°	1278.0
12°	1247.6
13°	1212.1
14°	1178.3
15°	1144.5
17.5°	1049.8
20°	956.8
22.5°	868.9
25°	784.4
27.5°	701.6
30°	617.0
32.5°	537.6
35°	454.8
37.5°	378.7
40°	306.0
42.5°	238.4
45°	179.2
47.5°	133.6
50°	96.4
52.5°	72.7
55°	59.2
57.5°	54.1
60°	47.3
62.5°	42.3
65°	37.2
67.5°	32.1
70°	27.0
72.5°	23.7
75°	18.6
77.5°	15.2
80°	11.8
82.5°	8.5
85°	5.1
87.5°	1.7



TEST NUMBER: P1252660

CATALOG NUMBER: P3AS20R259030D010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)