

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251823

Luminaire Tested: P3AS10R129030DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS10R129030DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 423.0 lumens
Efficiency: N/A
Efficacy: 36.2 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251823

CATALOG NUMBER: P3AS10R129030DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1251823

CATALOG NUMBER: P3AS10R129030DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182398
5°	168589
10°	134600
15°	101680
20°	77427
25°	59011
30°	42260
35°	27572
40°	16917
45°	10234
50°	6789
55°	5238
60°	4517
65°	3943
70°	3526
75°	3474
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10234 cd/sqm

TEST NUMBER: P1251823

CATALOG NUMBER: P3AS10R129030DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.8	16.0
10°-20°	125.2	29.6
20°-30°	111.5	26.3
30°-40°	65.9	15.6
40°-50°	27.1	6.4
50°-60°	12.7	3.0
60°-70°	7.7	1.8
70°-80°	4.1	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.5	72.0
0°-40°	370.4	87.6
0°-60°	410.2	97.0
0°-90°	423.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	832	
5°	766	68
15°	448	125
25°	244	111
35°	103	66
45°	33	27
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1251823

CATALOG NUMBER: P3AS10R129030DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	831.8
1°	829.8
2°	823.6
3°	811.2
4°	790.6
5°	765.9
6°	739.1
7°	707.5
8°	674.5
9°	640.9
10°	604.5
12.5°	521.4
15°	447.9
17.5°	384.7
20°	331.8
22.5°	285.1
25°	243.9
27.5°	204.0
30°	166.9
32.5°	133.3
35°	103.0
37.5°	79.0
40°	59.1
42.5°	44.0
45°	33.0
47.5°	25.4
50°	19.9
52.5°	16.5
55°	13.7
57.5°	11.7
60°	10.3
62.5°	8.9
65°	7.6
67.5°	6.9
70°	5.5
72.5°	4.8
75°	4.1
77.5°	2.7
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)