

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251855

Luminaire Tested: P3AS13R129030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 535.0 lumens
Efficiency: N/A
Efficacy: 34.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251855

CATALOG NUMBER: P3AS13R129030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251855

CATALOG NUMBER: P3AS13R129030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		93
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		86
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		80
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		75
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		70
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		66
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		62
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230705
5°	213229
10°	170226
15°	128582
20°	97915
25°	74617
30°	53451
35°	34880
40°	21383
45°	12932
50°	8597
55°	6652
60°	5701
65°	4981
70°	4488
75°	4406
80°	3283
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12932 cd/sqm

TEST NUMBER: P1251855

CATALOG NUMBER: P3AS13R129030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	16.0
10°-20°	158.3	29.6
20°-30°	140.9	26.3
30°-40°	83.4	15.6
40°-50°	34.2	6.4
50°-60°	16.1	3.0
60°-70°	9.8	1.8
70°-80°	5.2	1.0
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.1	72.0
0°-40°	468.5	87.6
0°-60°	518.8	97.0
0°-90°	535.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	535.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1052	
5°	969	86
15°	566	158
25°	308	141
35°	130	83
45°	42	34
55°	17	16
65°	10	10
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1251855

CATALOG NUMBER: P3AS13R129030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1052.1
1°	1049.5
2°	1041.7
3°	1026.0
4°	1000.0
5°	968.7
6°	934.8
7°	894.8
8°	853.1
9°	810.6
10°	764.5
12.5°	659.4
15°	566.4
17.5°	486.5
20°	419.6
22.5°	360.5
25°	308.4
27.5°	258.0
30°	211.1
32.5°	168.5
35°	130.3
37.5°	99.9
40°	74.7
42.5°	55.6
45°	41.7
47.5°	32.1
50°	25.2
52.5°	20.9
55°	17.4
57.5°	14.8
60°	13.0
62.5°	11.3
65°	9.6
67.5°	8.7
70°	7.0
72.5°	6.1
75°	5.2
77.5°	3.5
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)