

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251862

Luminaire Tested: P3AS13R159030DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159030DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1229.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251862

CATALOG NUMBER: P3AS13R159030DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1251862

CATALOG NUMBER: P3AS13R159030DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94	94	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	91	91	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	89	89	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	86	86	86
9	97	92	89	87	97	92	89	87	91	88	86	90	88	86	90	87	86	85	85	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	84	84	84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2388888
5°	2002108
10°	943069
15°	284338
20°	105196
25°	40914
30°	15243
35°	4685
40°	1660
45°	899
50°	648
55°	726
60°	833
65°	519
70°	641
75°	847
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 899 cd/sqm

TEST NUMBER: P1251862

CATALOG NUMBER: P3AS13R159030DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	703.2	57.2
10°-20°	418.0	34.0
20°-30°	87.8	7.1
30°-40°	14.2	1.2
40°-50°	2.4	0.2
50°-60°	1.7	0.1
60°-70°	1.1	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.0	98.4
0°-40°	1223.1	99.5
0°-60°	1227.2	99.9
0°-90°	1229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1229.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10894	
5°	9096	703
15°	1252	418
25°	169	88
35°	18	14
45°	3	2
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1251862

CATALOG NUMBER: P3AS13R159030DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	10894.2
1°	10860.2
2°	10687.2
3°	10341.3
4°	9834.1
5°	9095.6
6°	8228.0
7°	7235.9
8°	6288.5
9°	5215.8
10°	4235.4
12.5°	2285.3
15°	1252.5
17.5°	733.6
20°	450.8
22.5°	275.9
25°	169.1
27.5°	102.0
30°	60.2
32.5°	34.0
35°	17.5
37.5°	9.7
40°	5.8
42.5°	3.9
45°	2.9
47.5°	1.9
50°	1.9
52.5°	1.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)